



Full Length Article

Sb/Mn co-doped oxyfluoride silicate glasses for potential applications in photosynthesis

Chaofeng Zhu^{a,b}, Xianghua Zhang^{b,*}, Hongli Ma^b^a Key Laboratory of Processing and Testing Technology of Glass & Functional Ceramics of Shandong Province, Qilu University of Technology, Jinan 250353, P.R. China^b Laboratoire des Verres et Céramiques, UMR-CNRS 6226, Université de Rennes 1, Rennes 35042, France

ARTICLE INFO

Article history:

Received 11 September 2015

Received in revised form

4 November 2015

Accepted 5 November 2015

Available online 2 December 2015

Keywords:

Luminescence

Glasses

Photosynthesis

Energy transfer

ABSTRACT

A series of Sb/Mn co-doped oxyfluoride silicate glasses were prepared via the melt-quenching method to explore red luminescent materials for potential applications in photosynthesis of green plants, and these glasses are investigated by means of luminescence decay curves, absorption, emission, and excitation spectra. We find that the as-prepared glasses are transparent in the visible region and can emit strong red light under ultraviolet, purple, and green light excitations. Furthermore, energy transfer from Sb^{3+} to Mn^{2+} ions occurs in Sb/Mn co-doped glasses. The results demonstrate that the as-prepared Sb/Mn co-doped oxyfluoride silicate glasses may serve as a potential candidate for developing glass greenhouse, which can enhance the utilization of solar energy for the photosynthesis of the green plants.

© 2015 Elsevier B.V. All rights reserved.

1. Introduction

Photosynthesis is a process to convert light energy, normally from the sun, into chemical energy that can be later released to fuel the plants' activities. In the solar spectrum, the energy percentage of the ultraviolet (UV), visible, and infrared lights is about 7%, 50%, and 43%, respectively [1]. Generally, the green plants (chlorophylls) absorb more red light than other wavelengths for the photosynthesis. In addition, the green light can hardly be absorbed by the green plants for photosynthesis and the UV light is harmful to the growth of the plants. The lights absorbed by green plants for photosynthesis are only a very small portion in the whole solar spectrum [2,3]. Thus, to convert the UV and green lights into red light is a very promising and valuable work for the growth of the plants. At present, most greenhouses are made of the plastic materials, which have some drawbacks such as short lifetime, poor transparency, and instability. In recent years, the glass greenhouses are attracting more and more research attention due to the superior light transmittance, low production cost, and long service life compared to plastic greenhouses [2,3]. In particular, luminescent glasses can be used for the realization of solar spectrum modification, e.g., to convert the ultraviolet and green lights into the red light for photosynthesis. In other words, luminescent glasses are strongly expected to be an interesting and

excellent alternative approach to fabricate greenhouses compared to traditional plastic materials.

The oxyfluoride silicate glasses possess excellent chemical stability, good mechanical strength, high transparency for visible light, as well as low phonon energy environment for luminescence ions [4,5]. Sb and Mn are regarded as promising low-cost and environmental-friendly elements compared to rare earth. Additionally, Sb_2O_3 can also be used as a fining agent in glass melting. Based on above considerations, herein we fabricated a series of Sb- and Mn-doped oxyfluoride silicate glasses for greenhouse application and the optical properties of the glasses are investigated. Although some preliminary works on the luminescent glasses or glass-ceramics for greenhouses have been reported [2,3], the Sb/Mn co-doped oxyfluoride silicate glasses have not been considered for photosynthesis applications yet.

2. Experimental

All the investigated glasses have the glass matrix (GM) composition of $45\text{SiO}_2\text{--}15\text{Al}_2\text{O}_3\text{--}10\text{ZnO--}20\text{CaF}_2\text{--}10\text{CaO}$ (in mol%). Samples GMS2 (doped with 2 mol% Sb), GMM4 (doped with 4 mol% Mn), GMS2M2 (co-doped with 2 mol% Sb and 2 mol% Mn), GMS2M4 (co-doped with 2 mol% Sb and 4 mol% Mn), and GMS2M6 (co-doped with 2 mol% Sb and 6 mol% Mn) were prepared by a melt-quenching method. The chemicals SiO_2 , Al_2O_3 , ZnO , CaF_2 , CaCO_3 , Sb_2O_3 , and MnCO_3 were used as raw materials

* Corresponding author.

E-mail address: xiang-hua.zhang@univ-rennes1.fr (X. Zhang).

and they are analytical grade reagents. The starting materials calculated based on the compositions of the as-designed samples were taken in an agate mortar and grounded well to obtain homogenous mixtures. The homogenous batches were put into corundum crucibles and melted in an electrical furnace at 1460 °C for 1 h in air atmosphere. After melting, the glass melts were quickly casted into a preheated stainless steel mold for quenching. To relieve the internal stress of these glasses, which is induced during the quenching process, the obtained glasses were annealed at 450 °C for 2 h in air atmosphere, followed by natural cooling.

The energy dispersive spectroscopy (EDS) was measured using an EDS detector attached on the Scanning Electron Microscope (SEM, Hitachi S-4800, Japan) to analyze the compositions of the glasses. The absorption spectra were recorded using a Lambda 1050 UV/VIS/NIR spectrometer (PerkinElmer, USA). The excitation and emission spectra were measured using an FLS920 fluorescence spectrometer (Edinburgh Instruments Ltd., UK) using a 450 W Xe lamp (Xe900) as light source. The fluorescence decay curves were measured by using a standard storage digital oscilloscope and by exciting the samples at 266 nm with a frequency-quadrupled Nd: YAG laser providing 6 ns laser pulses. All the measurements were performed at room temperature with the same experimental parameters.

3. Results and discussion

Since some raw materials, e.g., CaF_2 and ZnO , can be volatile during the melting process, the final compositions of as-prepared glasses may deviate the nominal ones as designed. All the mentioned glasses in this paper have the identical glass matrix compositions. As an example, we carried out the composition analysis of sample GMS2 using EDS technique, as shown in Fig. 1. It can be seen that the content of F, Zn, and Sb decreased compared to the nominal compositions, indicating that these three elements were partially lost during preparing these glasses by the melt quenching method.

Fig. 2 shows the absorption spectra of samples GMS2, GMS2M2, GMS2M4, and GMS2M6 in the wavelength region of 200–800 nm. The samples present distinct absorption from 200 to 300 nm, which can be attributed to the partially forbidden electronic transition $^1\text{S}_0 \rightarrow ^3\text{P}_1$ of Sb^{3+} ions [6]. The absorption peaks at 415 nm shown in the inset are due to the electronic transition of $^6\text{A}_{1g} \rightarrow [^4\text{A}_{1g}; ^4\text{E}_g]$ of Mn^{2+} ions [7]. We can see that the glasses are highly transparent in the visible range and demonstrate intense absorption in the ultraviolet region, which indicates that the as-prepared glasses can efficiently absorb the ultraviolet light, and transmit the visible light. These optical features of the glasses are very helpful and effective for the protection, the growth and photosynthesis enhancement of the greenhouse plants.




Fig. 1. EDS spectrum of sample GMS2. The inset shows the comparison of the nominal and EDS measured element content.




Fig. 2. Absorption spectra of the glasses. The inset shows the enlarged absorption spectra in the range of 360–500 nm.




Fig. 3. Excitation and emission spectra of sample GMS2M4. The electronic transitions, excitation (λ_{ex}) and the monitored (λ_{em}) wavelengths are explicitly indicated in the figure.

In order to investigate the possibility of the Sb/Mn co-doped glass to convert the UV–purple–green lights into red light, we measured the excitation and emission spectra of sample GMS2M4, as shown in Fig. 3. The excitation spectrum monitored at 652 nm mainly contains four excitation bands. A broad excitation band at ~ 255 nm is due to the electronic transition of $^1\text{S}_0 \rightarrow ^3\text{P}_1$ of Sb^{3+} . The additional three excitation bands peaking at ~ 353 , 415, and 507 nm correspond to the electronic transitions from ground state $^6\text{A}_{1g}$ to excited states $^4\text{T}_{2d}$, $[^4\text{A}_{1g}; ^4\text{E}_g]$, and $^4\text{T}_{2g}$ of Mn^{2+} , respectively [8]. To further examine the potential application of the glass in greenhouse, we measured the emission spectra under the excitation of 255, 353, 415, and 507 nm, respectively, which correspond to the respective excitation peaks of sample GMS2M4. It can be seen that the shapes of the emission spectra under aforementioned excitation wavelengths are nearly the same except for the emission intensities. The emissions are attributed to the electronic transitions of $^4\text{T}_{1g} \rightarrow ^6\text{A}_{1g}$ of Mn^{2+} ions [9]. The energy ratios of the UV and green lights are $\sim 7\%$ and $\sim 10\%$ in the solar spectrum, which are waste for the photosynthesis of the green plants. Thus, it is very interesting to transfer the UV and green lights into the red light, which is helpful for photosynthesis. We can see in Fig. 3 that the as-prepared glasses can effectively convert the UV and blue–green lights into red emission, implying that

Download English Version:

<https://daneshyari.com/en/article/5398695>

Download Persian Version:

<https://daneshyari.com/article/5398695>

[Daneshyari.com](https://daneshyari.com)